

QUATRO

Part of Absolent Air Care Group



DUST COLLECTORS AND FUME EXTRACTORS
ACCESSORIES
FOR DENTAL APPLICATIONS



LED Magnifier / Debris Shield with Magnetic Base

Illuminates work area and improves visibility

Item #: AA555

Dimensions: 7 in (18 cm) diameter, 14 in (35 cm) arm

Shipping Weight: 2 lb (1 kg)

Electrical: 120-240 V, 0.3 A

- » 3 Functions: illumination, 2X magnification and debris shield
- » LEDs around perimeter of magnifier provide ideal lighting for work area
- » Integrated On/Off switch
- » Flexible arm extends 14" from base
- » Attaches to any ferromagnetic surface (iron/steel)
- » Included: 120-240 V adapter (#AA193), steel plate with 4 wood screws (#H125) if metal surface not available
- » Optional: 12 in (30 cm) arm extension (#AA429)

Magnifier / Debris Shield with Magnetic Base


Better visibility and protection from debris

Item #: AA427-12

Dimensions: 7 in (18 cm) diameter, 14 in (35 cm) arm

Shipping Weight: 2 lb (1 kg)

- » Dual purpose: 2X magnification and debris shield
- » Flexible arm extends 14" from base
- » Attaches to any ferromagnetic surface (iron/steel)
- » Included: steel plate with 4 wood screws (#H125) in case metal surface not available
- » Optional: 12 in (30 cm) arm extension (#AA429)



1.877.978.2876 · quatroair.com



1

AirZone Lo-Profile

Low Profile Attachment Fits In Your Drawer
Item #: AA754

Dimensions (HxWxL): 2x10x6.5 in (5x25x17 cm)
Shipping Weight: 3 lb (1 kg)

- » Low profile, 2 in high, shield also available
- » AA075-1.5S with shield
- » Powder coated heavy duty steel
- » Connects to your dust collector: 1.5", 2", 2.5" or 3" dia. hose
- » Optional Shields:
3x4"(h) #AR198, 8.75x8.75"(h) #AR198, 6x8.75"(h) #AR196
- » Also available with integrated Automatic Start Valve (#AA754-ASV)
or integrated Manual Slide Valve (#AA754-MSV)
- » Optional Upgrade Kit #2-0008-0011
adds Manual Shut-off Valve (MSV) to this accessory
- » Optional Upgrade Kit #2-0008-0012
adds Auto-Start Valve (ASV) to this accessory



AirZone Dust Hood, Space-Saving Containment System

Capture your zirconia disk blowout and keep room clean and healthy!
Item #: AA731

Dimensions (HxWxL): 9x10x6.5 in (23x25x17 cm)
Shipping Weight: 6 lb (3 kg)

- » Compact containment enclosure
- » Downdraft airflow helps keep contaminants away from breathing zone
- » Clear-Wall design: high visibility transparent walls
- » Hinged face shield swings up and away for better visibility
- » Gasket cushions for ergonomic hand support
- » Connects to your dust collector: 1.5", 2", 2.5" or 3" diameter hose
- » Also available with integrated Automatic Start Valve (#AA731-ASV)
or integrated Manual Slide Valve (#AA731-MSV)
- » Optional Upgrade Kit #2-0008-0011
adds Manual Shut-off Valve (MSV) to this accessory
- » Optional Upgrade Kit #2-0008-0012
adds Auto-Start Valve (ASV) to this accessory

AirZone with LED Magnifier, Air Attachment For Hand-piece

Downdraft airflow helps keep contaminants away from breathing zone
Item #: AA760

Dimensions (HxWxL): 12x10x6.5 in (31x25x17 cm)
Shipping Weight: 6 lb (3 kg)
Electrical: 120-240 V, 60 Hz, 0.3 A

- » Bright LED illuminated, with ON/OFF switch
- » Adjustable magnifier mounts separately onto accessory
- » LED Magnifier also serves as debris shield
- » Gasket cushions for ergonomic hand support
- » Connect to your dust collector: 1.5", 2", 2.5" or 3" diameter hose
- » Included: LED Magnifier with 120-240 V adapter (#AA555-17)
- » Also available with integrated Automatic Start Valve (#AA760-ASV)
or integrated Manual Slide Valve (#AA760-MSV)
- » Optional Upgrade Kit #2-0008-0011
adds Manual Shut-off Valve (MSV) to this accessory
- » Optional Upgrade Kit #2-0008-0012
adds Auto-Start Valve (ASV) to this accessory




Front Suction Adapter

Workbench Attachment at the Front of the Bench
Item #: AA709

Dimensions (HxWxL): 9.5x6.5x7.5 in (24x17x19 cm)
Shipping Weight: 2 lb (1 kg)

- » Secure to underside of workbench, grille faces away from user
- » Shield keeps fine particles away from breathing zone
- » Connects to your dust collector: 1.5", 2", 2.5" or 3" diameter hose
- » Included: 3x4 in shield (#AR105)
- » Optional, larger shields: 8.75x8.75"(h) #AR198, 6x8.75"(h) #AR196
- » Also available with integrated Automatic Start Valve (#AA709-ASV) or integrated Manual Slide Valve (#AA709-MSV)
- » Optional Upgrade Kit #2-0008-0011 adds Manual Shut-off Valve (MSV) to this accessory
- » Optional Upgrade Kit #2-0008-0012 adds Auto-Start Valve (ASV) to this accessory



AirPort Lo-Profile

Downdraft airflow helps keep contaminants away from breathing zone
Item #: AA765

Dimensions (HxWxL): 3.5x10x9 in (90x25x23 cm)
Shipping Weight: 5 lb (2 kg)

- » Gasket cushions for ergonomic hand support
- » Powder coated heavy duty steel
- » To attach a Slide-Valve, call for part number, depends on connecting hose
- » Connects to your dust collector: 1.5", 2", 2.5" or 3" dia, hose
- » Also available with integrated Automatic Start Valve (#AA765-ASV) or integrated Manual Slide Valve (#AA765-MSV)
- » Optional Upgrade Kit #2-0008-0011 adds Manual Shut-off Valve (MSV) to this accessory
- » Optional Upgrade Kit #2-0008-0012 adds Auto-Start Valve (ASV) to this accessory

AirPort Dust Hood, Space-Saving Containment System

Capture your zirconia disk blowout and keep room clean and healthy!
Item #: AA732

Dimensions (HxWxL): 9x10x9 in (23x25x23 cm)
Shipping Weight: 6 lb (3 kg)

- » Compact containment enclosure
- » Clear-Wall design: high visibility transparent walls
- » Downdraft airflow helps keep contaminants away from breathing zone
- » Hinged face shield swings up and away for better visibility
- » Gasket cushions for ergonomic hand support
- » Connects to your dust collector: 1.5", 2", 2.5" or 3" diameter hose
- » Also available with integrated Automatic Start Valve (#AA732-ASV) or integrated Manual Slide Valve (#AA732-MSV)
- » Optional Upgrade Kit #2-0008-0011 adds Manual Shut-off Valve (MSV) to this accessory
- » Optional Upgrade Kit #2-0008-0012 adds Auto-Start Valve (ASV) to this accessory



AirPort with LED Magnifier, Workbench Air Attachment

Downdraft airflow helps keep contaminants away from breathing zone
Item #: AA722

Dimensions (HxWxL): 12x10x9 in (31x25x23 cm)
Shipping Weight: 10 lb (5 kg)
Electrical: 100-120 V, 60 Hz, 0.3 A

- » Bright LED illuminated, with ON/OFF switch
- » Adjustable magnifier mounts separately onto accessory
- » LED Magnifier also serves as debris shield
- » Gasket cushions for ergonomic hand support
- » Connect to your dust collector: 1.5", 2", 2.5" or 3" diameter hose
- » Included: LED Magnifier with 120-240 V adapter (#AA555-17)
- » Also available with integrated Automatic Start Valve (#AA722-ASV) or integrated Manual Slide Valve (#AA722-MSV)
- » Optional Upgrade Kit #2-0008-0011 adds Manual Shut-off Valve (MSV) to this accessory
- » Optional Upgrade Kit #2-0008-0012 adds Auto-Start Valve (ASV) to this accessory

Suction Wedge, Workbench Attachment at the Front of the Bench

Downdraft airflow helps keep contaminants away from breathing zone
Item #: AA343

Dimensions (WxL): 2.63x5.38 in (7x14 cm)
Shipping Weight: 6 lb (3 kg)

- » Wood wedge installs in front of bench
- » Wire mesh prevents items from being drawn in
- » Connects to 1.5 in diameter hose below
- » Under-the-counter support makes it easy to remove when not needed
- » Included: Steel under-the-counter support (#AA344)
- » Also available: Suction Wedge only, without steel under-the-counter support (#AA213)



SplashGuard with LED Magnifier

Air Attachment For Lathe
Item #: AA783

Dimensions (HxWxL): 12x8x14.5 in (31x20x37 cm)
Shipping Weight: 6 lb (3 kg)
Electrical: 100-120 V, 60 Hz, 0.3 A

- » Bright LED illuminated, with ON/OFF switch
- » LED frontal illumination does not cast shadow on objects worked on
- » LED magnifier also serves as debris shield
- » LED shield/magnifier (2X magnification) is fully adjustable
- » Connects to 1.5", 2", 2.5" or 3" diameter hose
- » Included: 120-240 V adapter (#AA193), SplashPan (#AR073)
- » Optional: Manual slide version #AA783-MSV, Auto-Start Valve version: #AA783-ASV
- » Optional Upgrade Kit #2-0008-0011 adds Manual Shut-off Valve (MSV) to this accessory
- » Optional Upgrade Kit #2-0008-0012 adds Auto-Start Valve (ASV) to this accessory



SplashGuard LED with Protective Face Shield

Air Attachment For Lathe
Item #: AA883

Dimensions (HxWxL): 12x8x14.5 in (31x20x37 cm)
Shipping Weight: 6 lb (3 kg)
Electrical: 100-120 V, 60 Hz, 0.3 A

- » Bright LED illuminated, with ON/OFF switch
- » Powder coated heavy duty steel
- » Connects to 1.5", 2", 2.5" or 3" diameter hose
- » Replacement Shield available (#AA103)
- » #AA883-MSV SplashGuard LED with Manual Slide Valve included
- » #AA883-ASV SplashGuard LED with Auto-Start Valve included
- » Included: 120-240 V power adapter (#AA193), LED light strip (#AA109), and SplashPan (#AR073)
- » Optional Upgrade Kit #2-0008-0011 adds Manual Shut-off Valve (MSV) to this accessory
- » Optional Upgrade Kit #2-0008-0012 adds Auto-Start Valve (ASV) to this accessory

Fishmouth

Conventional Workbench Air Attachment
Item #: AA751

Dimensions (HxWxL): 5x8.5x9 in (13x22x23 cm)
Shipping Weight: 3 lb (1 kg)

- » Powder coated heavy duty steel
- » Wire mesh keeps parts from being drawn in
- » Connects to your dust collector: 1.5", 2", 2.5" or 3" diameter hose
- » Also available with integrated Automatic Start Valve (#AA751-ASV) or integrated Manual Slide Valve (#AA751-MSV)
- » Optional Upgrade Kit #2-0008-0011 adds Manual Shut-off Valve (MSV) to this accessory
- » Optional Upgrade Kit #2-0008-0012 adds Auto-Start Valve (ASV) to this accessory




Fishmouth Mini

Compact Workbench Air Attachment
Item #: AA535

Dimensions (HxWxL): 4x6x5.5 in (10x15x14 cm)
Shipping Weight: 2 lb (1 kg)

- » Powder coated heavy duty steel
- » Attaches to a 1.5 in (38 mm) hose diameter
- » Compact is ideal for dentist
- » Smaller form factor, perfect for portability



LED ClearView Basic, Illuminated Workbench Containment Box

Connects to dust collector via 1.5 or 2 in diameter hose

Item #: 2-0058-0020,

Item #: 2-0058-0021 (w/MSV, manual valve included); 2-0058-0022 (w/ASV included)

Dimensions (HxWxD): 15x15.5x14.25 in (38x39x36 cm)

Shipping Weight: 17 lb (8 kg)

Electrical: 100-120 V, 60 Hz, 0.3 A

- » Eliminates debris from breathing zone, contains all debris within enclosure
- » Ideal applications: where harmful debris containment is essential
- » Included: 1.5 in / 2 in diameter inlet in rear
- » Optional: 2.5", 3", 4" diameter inlets; Side opening suited for working with lathe (#AR300-19); Hinged magnifier (#AA445); Adjustable capture nozzle (#AA240); Compressed air w/variable flow retrofit kit (#2-0058-0013)
- » ASV model: when used with appropriate QUATRO units, remotely starts-stops dust collector while you open/close the valve INSIDE the ClearView

LED ClearView Magnifier, Illuminated Workbench Containment Box

Connects to dust collector via 1.5 or 2 in diameter hose

Item #: 2-0058-0030



Item #: 2-0058-0031 (w/MSV, manual valve included); 2-0058-0032 (w/ASV included)

Dimensions (HxWxD): 15x15.5x14.25 in (38x39x36 cm)

Shipping Weight: 17 lb (8 kg)

Electrical: 100-120 V, 60 Hz, 0.3 A

- » Eliminates debris from breathing zone, contains all debris within enclosure
- » Hinged magnifier (7 in diameter, 2X magnification factor)
- » Adjustable source capture nozzle for efficient removal of fine particulate
- » Included: 1.5 in / 2 in diameter inlet in rear
- » Optional: 2.5", 3", 4" diameter inlets; Side opening suited for working with lathe (#AR300-19); Compressed air w/variable flow retrofit kit (#2-0058-0013)
- » ASV model: when used with appropriate QUATRO units, remotely starts-stops dust collector while you open/close the valve INSIDE the ClearView



LED ClearView Milling, Illuminated Workbench Containment Box

Connects to dust collector via 1.5 or 2 in diameter hose

Item #: 2-0058-0040

Item #: 2-0058-0041 (w/MSV, manual valve included); 2-0058-0042 (w/ASV included)

Dimensions (HxWxD): 15x15.5x14.25 in (38x39x36 cm) · Shipping Weight: 17 lb (8 kg)

Electrical: 100-120 V, 50/60 Hz, 0.3 A

- » Eliminates debris from breathing zone, contains all debris within enclosure
- » Hinged magnifier (7 in diameter, 2X magnification factor)
- » Adjustable source capture nozzle for efficient removal of fine particulate
- » Easy connection to compressed air line (compressed air line can be attached to either side)
- » Variable flow compressed air accessories included: air gun, valve and tubing ("Push-to-connect", 1/4" dia)
- » Included: 1.5 in / 2 in diameter inlet in rear
- » Optional: 2.5", 3", 4" diameter inlets; Side opening suited for working with lathe (#AR300-19)
- » ASV model: when used with appropriate QUATRO units, remotely starts-stops dust collector while you open/close the valve INSIDE the ClearView

LED AirBox, Illuminated Desktop Containment System

Keep a clean and healthy work environment by containing dust, odor and debris

Item #: AA266-1S+, Space-saving LED AirBox

Item #: AA266-2S+, Full-size LED AirBox

Dimensions (HxWxD): 14.5x24x17.5 in (37x61x45cm) (Space-saving Box)

Dimensions (HxWxD): 24x29x20 in (61x74x51cm) (Full-size Box)

- » Bright LED illuminated, with ON/OFF switch
- » LED can be installed on top or either side of box
- » Hinged doors swing up and away for easy access
- » Powder coated heavy duty steel
- » Connect to your dust collector via 1.5", 2", 2.5" or 3" diameter hose.
Please specify required diameter when placing the order.
- » Included: LED power adapter. Please specify country/voltage when placing the order.
- » Also available with integrated Automatic Start Valve or integrated Manual Slide Valve



Deluxe Mobile Arm, Move it out of the way when not in use

Connects to 2.5 in diameter hose
Item #: AA009

Shipping Weight: 5 lb (2 kg)

- » Installs on your workbench
- » Extends to 24 in long, holds its own weight
- » Included: Table-bracket (#M042) connects to 2.5 in hose, Plexi wide nozzle (#AA043)
- » Optional: SlideValve (#H397)



Deluxe Mobile Arm, Move it out of the way when not in use

Connects to 1.5 in diameter hose
Item #: AA326

Shipping Weight: 5 lb (2 kg)

- » Mounts on your workbench
- » Extends to 24 in long, holds its own weight
- » Included: Table-bracket (#M410) connects to 1.5 in hose, Plexi wide nozzle (#AA043)
- » Optional: SlideValve (#H397)



ASV Capture Arms

Airflow control AND remotely start/stop dust collector at each workstation
Connect several ASVs to one dust collector to accommodate multiple workstations

Shipping Weight: 2 lb (1 kg)

- » Slide Valve opens and closes for a dual purpose:
Controls suction by blocking airflow at idle workstations
Remotely switches dust collector on and off at each workstation
- » Connect as many ASVs as needed to one dust collector
- » Dust collector will remain on as long as one valve is open
- » REAR COLLAR DIAMETERS CAN VARY (1.5 in, 2 in, 2.5 in or 3 in)
- » Included: Inlet Nozzle (see table below), Table-Stand Support Bracket (#AA423), 25 ft long cable
- » Optional: Cable to connect to unit (#AE750) (1 cable per unit)



PART NUMBER SELECTION GUIDE		FRONT DIAMETER 3"		
		8" Plexi Nozzle	4" Round Nozzle	1.5" Oval Nozzle
REAR DIAMETER	1.5"	AA433P-A31-20	AA433R-A31-20	AA4330-A31-20
	2"	AA433P-A32-20	AA433R-A32-20	AA4330-A32-20
	2.5"	AA433P-A35-20	AA433R-A35-20	AA4330-A35-20
	3"	AA433P-A33-20	AA433R-A33-20	AA4330-A33-20



ASV (Auto Start Valve)

Airflow control AND remotely start/stop dust collector at each workstation
Connect several ASVs to one dust collector to accommodate multiple workstations

Dimensions (HxWxL): 6.2x7.3x2.5 in (16x19x6 cm)
 Shipping Weight: 2 lb (1 kg)

- » Slide Valve opens and closes for a dual purpose:
 Controls suction by blocking airflow at idle workstations
 Remotely switches dust collector on and off at each workstation
- » Connect as many ASVs as needed to one dust collector. Dust collector will remain on as long as one valve is open
- » Clamp or bolt ASVs directly to workbench
- » FRONT AND REAR COLLAR DIAMETERS CAN VARY (1.5 in, 2 in, 2.5 in or 3 in)
- » Included: 25 ft cable (10 ft cable also available)
- » Optional: Table-Stand Support Bracket (#AA423), Cable to connect to unit (#AE750) (1 cable per unit)

PART NUMBER SELECTION GUIDE		FRONT DIAMETER			
		1.5"	2"	2.5"	3"
REAR DIAMETER	1.5"	AA413-A11-20	AA413-A21-20	AA413-A51-20	AA413-A31-20
	2"	AA413-A12-20	AA413-A22-20	AA413-A52-20	AA413-A32-20
	2.5"	AA413-A15-20	AA413-A25-20	AA413-A55-20	AA413-A35-20
	3"	AA413-A13-20	AA413-A23-20	AA413-A53-20	AA413-A33-20

ASV (Auto Start Valve) with integrated support stand

Airflow control AND remotely start/stop dust collector at each workstation
Connect several ASVs to one dust collector to accommodate multiple workstations

Dimensions (HxWxL): 6.2x7.3x2.5 in (16x19x6 cm)
 Shipping Weight: 2 lb (1 kg)

- » Slide Valve opens and closes for a dual purpose:
 Controls suction by blocking airflow at idle workstations
 Remotely switches dust collector on and off at each workstation
- » Connect as many ASVs as needed to one dust collector. Dust collector will remain on as long as one valve is open
- » Clamp or bolt the integrated support stand directly to workbench
- » FRONT AND REAR COLLAR DIAMETERS CAN VARY (1.5 in, 2 in, 2.5 in or 3 in)
- » Included: 25 ft cable (10 ft cable also available)
- » Optional: Cable to connect to unit (#AE750) (1 cable per unit)



PART NUMBER SELECTION GUIDE		FRONT DIAMETER			
		1.5"	2"	2.5"	3"
REAR DIAMETER	1.5"	AA433-A11-20	AA433-A21-20	AA433-A51-20	AA433-A31-20
	2"	AA433-A12-20	AA433-A22-20	AA433-A52-20	AA433-A32-20
	2.5"	AA433-A15-20	AA433-A25-20	AA433-A55-20	AA433-A35-20
	3"	AA433-A13-20	AA433-A23-20	AA433-A53-20	AA433-A33-20

MSV (Manual Slide Valve)

Airflow control at each workstation

Dimensions (HxWxL): 3x7.3x2.5 in [8x19x6 cm]
Shipping Weight: 5 lbs [2 kg]

- » Shut Off Airflow When Not Using
- » For manual Open-Close operation
- » Shut-off work-station when not in use, increase suction power to other work-stations or attachments
- » CAN BE BUILT IN ANY DIAMETER (Front and Rear can be different diameters)
- » Optional: Support stand to mount onto existing valve is sold separately (#AA423)



PART NUMBER SELECTION GUIDE		FRONT DIAMETER		
		1.5"	2"	3"
REAR DIAMETER	1.5"	AA413-M11	AA413-M21	AA413-M31
	2"	AA413-M12	AA413-M22	AA413-M32
	3"	AA413-M13	AA413-M23	AA413-M33



MSV (Manual Slide Valve) with integrated support stand

Airflow control at each workstation

Dimensions (HxWxL): 5x7.3x2.5 in [12.7x19x6 cm]
Shipping Weight: 5 lbs [2 kg]

- » Can be conveniently bolted OR clamped down to secure
- » Shut off airflow when not using
- » For manual open/close operation
- » Shut-off workstation when not in use, increase suction power to other workstations or attachments
- » Valve INCLUDES integrated support stand
- » CAN BE BUILT IN ANY DIAMETER (front and rear can be different diameters)

PART NUMBER SELECTION GUIDE		FRONT DIAMETER		
		1.5"	2"	3"
REAR DIAMETER	1.5"	AA433-M11	AA433-M21	AA433-M31
	2"	AA433-M12	AA433-M22	AA433-M32
	3"	AA433-M13	AA433-M23	AA433-M33



Cyclone Collector, Cyclonic Separation Strips Out Larger Particles

Extend the life of your filter bags, reduce dust collector maintenance
Item #: AA249

Dimensions (HxWxL): 27x12x12 in (69x30x30 cm)
Shipping Weight: 8 lb (4 kg)

- » Use with any dust collection (except Velocity) for high debris applications
- » Cyclonic separation of particles
- » Connects between attachment and dust collector
- » Ideal for sandblasters and dry model trimmers
- » Holds up to 0.8 ft³, 6 US gallons (23 litres)
- » Connect to your dust collector
- » Includes 6 ft of 2 in diameter hose (#H154-06)
- » Includes kit to reduce hose to 1.5 in diameter

Cut-Off (1-2 Station)

2-Way Air Diverter
Item #: AA250

Dimensions (HxWxL): 3x6.5x7.5 in (8x17x19 cm)
Shipping Weight: 3 lb (1 kg)

- » Get full airflow at one station by diverting the air from the other
- » Also can switch to 2 stations running simultaneously
- » Powder coated heavy duty steel
- » Connect to your dust collector, 1.5" diameter hose



Bench Downdraft Adapter

Adapter only
Item #: AA782

Dimensions (HxWxL): 3x4x6 in (76x10x15 cm)
Shipping Weight: 5 lb (2 kg)

- » Installs to underside of workbench
- » Ideal to install beneath drawer
- » Powder coated heavy duty steel
- » Connects to 1.5, 2, 2.5 or 3 inch diameter hose
- » Optional Upgrade Kit #2-0008-0011 adds Manual Shut-off Valve (MSV)
- » Optional Upgrade Kit #2-0008-0012 adds Auto-Start Valve (ASV)
- » #AA782-MSV - Bench Downdraft Adapter with Manual Slide Valve included
- » #AA782-ASV - Bench Downdraft Adapter with Auto-Start Valve include




AirTop

Workbench Air Attachment
Item #: A103

Dimensions (HxWxL): 7x11x6.5 in (18x28x17 cm)
Shipping Weight: 5 lb (2 kg)

- » Attaches to front top of workbench
- » Powder coated heavy duty steel
- » Gasket cushions for ergonomic hand support
- » Wire mesh screen keeps parts from being drawn in
- » To attach a ASV or MSV (Slide-Valve), contact us
- » Connects to your dust collector (1.5", 2", 2.5" diameter hose)
- » Dimensions (HxWxL): 7x11x6.5 in (18x28x17 cm)



FumeTrap

Source capture accessory helps keep contaminants away from breathing zone
Item #: H277

Dimensions (HxWxL): 8x12x6 in (20x31x15 cm)
Shipping Weight: 3 lb (1 kg)

- » Connects to MonoPure desktop odor eliminator
- » Contains odors within enclosure
- » Plexiglass, 4 in diameter connection in back



Universal On/Off Foot-Pedal

Remote start any device from 6 ft away (15 A max.)
Item #: H181

Shipping Weight: 1 lb (0.5 kg)

- » Pedal installs into 120 V wall outlet, device plugs into pedal
- » Conveniently remote start your device from 6 feet away
- » Start-stop of all equipment, directly from wall outlet
- » 15 amp (maintained & momentary)



Remote Foot-pedal

1-Station Foot-pedal
Item #: AA114 or AA175

Shipping Weight: 1 lb (0.5 kg)

- » Conveniently remote start unit from 6 feet away
- » AA114 for Velocity, JS0200, JS1200, Medevac Mini, DFH
- » AA175 for SmartVacs, IVACs, MMP, MP, PS Series



Remote Foot-pedal for 2-Stations

2-Station Foot-pedal
Item #: AA224 or AA442

Shipping Weight: 1 lb (0.5 kg)

- » Conveniently remote start unit from 6 feet away
- » Includes a wired "T" with (2) 6ft long foot-pedals
- » AA224 for Velocity, JS0200, JS1200, Medevac Mini, DFH
- » AA442 for SmartVacs, IVACs, MMP, MP, PS Series





On/Off Remote
1-Station Hand-switch
Item #: AA011 or AA375

Shipping Weight: 1 lb (0.5 kg)

- » Conveniently remote start unit from 6 feet away
- » AA011 for Velocity, JS0200, JS1200, Medevac Mini, DFH
- » AA375 for SmartVacs, IVACs, MMP, MP, PS Series

On/Off 2-Station Remote
2-Station Hand-switch
Item #: AA012 or AA432

Shipping Weight: 1 lb (0.5 kg)

- » Conveniently remote start unit from 6 feet away
- » 8 feet between stations
- » AA012 for Velocity, JS0200, JS1200, Medevac Mini, DFH
- » AA432 for SmartVacs, IVACs, MMP, MP, PS Series



Mini Noise Silencer
Install on air discharge to reduce noise
Item #: A081

Dimensions (HxWxL): 7x7x3 in (18x18x8 cm)
Shipping Weight: 3 lbs (1 kg)

- » Compatible with all Basic (BA), CollectAll(CA), MedEVAC (MMP) and iVAC models

Noise Reducing Silencer, installs on air discharge to reduce noise
Used on Velocity and DFH Units
Item #: H250

Dimensions (HxWxL): 12x13.5x3.25 in (30x34x8 cm)
Shipping Weight: 5 lb (2 kg)

- » Used on Velocity, DFH, MMP, PS2




3D Printer Containment Box


Keep a clean and healthy work environment by containing odor emitted by 3D printer
Item #: 2-0008-0377

Dimensions (HxWxL): 31x20.5x20 in (79x52x51 cm)

- » Bright LED illuminated, with ON/OFF switch
- » Hinged doors swing up and away for easy access
- » Powder coated heavy duty steel
- » Connect to your odor extractor via 3" diameter hose (other diameters available)



3D Printer
Not Included



3D Printer
Not Included

3D Printer Containment Box with Source Capture Purifier

Keep a clean and healthy work environment by containing odor emitted by 3D printer
Item #: 3-0016-0377

Dimensions (HxWxL): 31x20.5x20 in (79x52x51 cm)


- » **Includes Quatro MonoPure Fume Extractor**
- » Bright LED illuminated, with ON/OFF switch
- » Hinged doors swing up and away for easy access
- » Powder coated heavy duty steel
- » Connect to your odor extractor via 3" diameter hose (other diameters available)

3D Printer Containment Box with Source Capture Purifier & Flex Arm for Cleaning Station

Keep a clean and healthy work environment by containing odor emitted by 3D printer
Item #: 3-0016-0378

Dimensions (HxWxL): 31x20.5x20 in (79x52x51 cm)

- » **Includes Quatro MonoPure Fume Extractor and Flex Arm for Cleaning Station**
- » Bright LED illuminated, with ON/OFF switch
- » Hinged doors swing up and away for easy access
- » Powder coated heavy duty steel
- » Connect to your odor extractor via 3" diameter hose (other diameters available)



3D Printer
Not Included